

# Specifications



Photo is representative



## Eaton CHP32L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 64, 32, Three-wire, Single-phase

### General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CHP32L150R
UPC	786689058692
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



Powering Business Worldwide

Product specifications	
SPECIAL FEATURES	Cover included
TYPE	Main Lug Only
AMPERAGE RATING	150 A
BUS MATERIAL	Copper
FEED TYPE	Overhead
NUMBER OF CIRCUITS	64
NUMBER OF SPACES	32
PHASE	Single-phase
BOX SIZE	X5
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources	
MULTIMEDIA	<a href="#">AFCI Educational Video</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CHP32L150R</a>
WARRANTY GUIDES	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications



Photo is representative



## Eaton CHP32L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 64, 32, Three-wire, Single-phase

### General specifications

PRODUCT NAME	Eaton CH main lug loadcenter
CATALOG NUMBER	CHP32L150R
UPC	786689058692
PRODUCT LENGTH/DEPTH	29 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



Powering Business Worldwide

Product specifications	
SPECIAL FEATURES	Cover included
TYPE	Main Lug Only
AMPERAGE RATING	150 A
BUS MATERIAL	Copper
FEED TYPE	Overhead
NUMBER OF CIRCUITS	64
NUMBER OF SPACES	32
PHASE	Single-phase
BOX SIZE	X5
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

Resources	
MULTIMEDIA	<a href="#">AFCI Educational Video</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CHP32L150R</a>
WARRANTY GUIDES	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

