



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHP42E225X7 CH Pon Loadcnr 225A Convertible Lugs Inst 42 Spac

*Eaton Corp*

Catalog Number	CHP42E225X7
Manufacturer	Eaton Corp
Description	Eaton CH Pon 3/4-In Eaton CH Loadcenter, 225A, Convertible, Lugs Inst, 42 Spaces, Nema 1, Copper Bus, Top/Bottom Feed, X7, Single Phase, Three Wire
Weight per unit	21.6 (lbs/each)
Product Category	Single Phase Convertible Load

### Features

dimensions	37.0000 IN X 14.3100 IN X 3.8800 IN
Material	Metallic
media	Yes

### Descriptions

Description	CH PON LOADCNR 225A CONVERTIBLE LUGS INST 42 SPAC
extra long description	ETN CHP42E225X7 CH PON LC, 225A, CO
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH PON 3/4-in Eaton CH loadcenter, 225A, convertible, lugs inst, 42 spaces, NEMA 1, Copper bus, Top/bottom feed, X7, Single phase, three wire
Product Type	CH Pon LC, 225A, Conv, Lugs Inst, 42SP

### Manufacturer Information

Brand	Eaton
GTIN	00786679189740
Manufacturers Part Number	CHP42E225X7
UPC	786679189740

### Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Convertible loadcenter

### Packaging

Carton	1
Weight Per each	21.6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

UL 50,UL 67