



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CH2L125SP 1 PH/CH Loadctr 125A Mlo 2/4 Cir. Cu Bus Surface *Eaton Corp*

|                  |  |
|------------------|--|
| Catalog Number   | CH2L125SP  |
| Manufacturer     | Eaton Corp   |
| Description      | Main Lug Load Center, 2 Spaces, 2 Circuits, 125 A, 120/240 V Ac, #1 to 4/0 Awg Wire Size, Metallic Material, Copper Bus Material, 6.88 In Overall Length, 3.39 In Overall Width, 11.38 In Overall Height, Surface Mount (Trim), 3.3 LB |
| Weight per unit  | 3.3 (lbs/each)   |
| Product Category | Single Phase Main Lug Load Cen   |

### Features

|                  |           |
|------------------|-----------|
| amperage rating  | 125       |
| interrupt rating | 25        |
| media            | Yes       |
| Phase            | 1         |
| Wattage          | Four-pole |

### Dimensions and Weight

|        |      |
|--------|------|
| Depth  | 9.5  |
| Height | 3.13 |
| Size   | 6    |
| Width  | 4.5  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 1 PH/CH LOADCNTR 125A MLO 2/4 CIR. CU BUS SURFACE |
| extra long description | ETN CH2L125SP 1 Ph/CH LC 125A MLO 2               |

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN  | 00782114190470      |
| UPC   | 782114190470        |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | LOADCENTERS & COVERS |
| Type                 | Main lug loadcenter  |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 3.3 |

### Uses, Certifications, and Standards

|          |               |
|----------|---------------|
| Mounting | Surface Mount |
| standard | UL 67,UL 50   |