

PRODUCT OFFERING

QUALITY • VALUE • VERSATILITY





LED FAMILY

The Compass® LED product series includes economical energy saving fixtures suitable for use in any commercial or light industrial application. Value engineered to reduce cost without sacrificing quality. The Compass LED family provides a compact product offering that can be purchased and installed without compromise.

Quality


Long-life **LED** operation
Premium Nickel Cadmium battery
Low energy consumption

Value

Remote capacity option with matching remotes
Damp and wet location products
UL924 Listed
2 Year Warranty

Versatility

Fully adjustable optics
Bright and even EXIT illumination
Optimized spacing and coverage
Indoor and outdoor applications



Self-Test | Self-Diagnostics



Self-Diagnostic Features

Fault identification for battery, charge, LED integral lamps and remotes
 Self-Testing for 15 minutes monthly, and 90 minutes annually
 manual testing for 30 second, 15 minutes and 90 minutes

Self-Testing Features

15-minute discharge once every 30 days
 90-minute discharge once every year

Manual Testing

Action	Reaction and LED Indication
Push Test Button Once	30 Second test: FLASHING Green
Push Test Button Twice	15 Minute test: Green BLINKING Twice
Push Test Button Three Times	90 Minute test: Green BLINKING 3 Times

Fault Indication

Fault Description	LED IN
Battery Disconnected	Steady Red
Battery Recharge Failure	Flashing Red
Battery Failure	Blinking Red 2 Times
LED Failure	Blinking Red 3 Times
Lamp Failure	Blinking Red 4 Times
Remote Lamp Failure	Blinking Red 5 Times
Transfer Fault	Blinking Red 6 Times

Included on the following products:



Combo Exit/Emergency Light

CCRS
 CCGSD
 CCRRCS
 CCGRCS



Exit Sign

CERS
 CEGSD



Emergency Light

CU2S
 CU2RCS



Square Head Emergency Light

CU2SQS
 CU2RCSQS

- LED Life-cycle of more than 10 years
- Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Dual-voltage 120 or 277V AC input
- Provided with test switch and AC-On Indicator
- Canopy included



Products with this icon have optional Self-Test/
Self-Diagnostics available



- White or Black housing made of high impact UL flame rated thermoplastic
- Molded-in template for quick installation
- Lamp-heads are fully adjustable
- Remote capacity or extended run-time option
- Matching indoor or outdoor remote heads CIRS, CIRD, CORD, CORS
- Damp Location Listed



- Molded-in template for quick installation
- Universal single or double-face
- Remote capacity or extended run-time option
- Matching indoor or outdoor remote heads CIRS, CIRD, CORD, CORS
- Damp Location Listed



- White or Black housing made of high impact UL flame rated thermoplastic
- Molded-in template for quick installation
- Square Heads are fully adjustable
- Remote capacity or extended run-time option
- Matching indoor or outdoor remote heads CIRS, CIRD, CORD, CORS
- Damp Location Listed



- Housing and face plate made from impact resistant polycarbonate
- Corrosion resistant and faceplate fully gasketed
- Wall, End or Ceiling Mounted
- Wet location listed (-20°C to 50°C)
- Single or Double Face options



- Brushed Aluminum Housing with Acrylic Panels
- Panel illumination with red or green letters
- Mirror divider on single and double-face models
- Low input power consumption at 3.72 Watts
- Listed to UL924 Standard



- Brushed aluminum die-cast housing with 6" letters
- Molded-in template for quick installation
- Single or double-face options
- Wall, End or Ceiling Mounted
- 24 hr re-charge
- Damp Location Listed



- Exit face-plate and lamp-head shield made from high impact, UV stable polycarbonate
- LED based exit/emergency light for wall, ceiling or end mounting
- Includes Self-Test/Self-Diagnostics
- Fully adjustable LED lamp-heads at 3.6W each
- Wet Location Listed

- LED Life-cycle of more than 10 years
- Quick Installation
- 90 minute run-time
- Dual-voltage 120 or 277V AC input



- Low level or above the door with adjustable angle options
- 4.8Vdc Nickel Metal Hydride (NiMH) Battery
- Quick installation
- Mounts in a 4" square J-box
- Passive Infra-Red (PIR) sensor option for convenient night-light operation
- Optional Passive Infra-Red (PIR) sensor for night-light



- Housing made of white or black high impact UL flame rated thermoplastic
- Wall or Ceiling Mounted
- Fully adjustable square lamp-heads
- Remote capacity or extended run-time option
- Long Life Nickel Cadmium battery
- Provided with test switch and AC-On indicator



- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- The fixed optic design provides consistent and predictable aiming
- Damp Location Listed 20°C to 30°C (68°F to 86°F)
- Provided with test switch and AC-On indicator
- Wall or Ceiling mount



- Grey or Black housing
- Corrosion resistant UV stabilized polycarbonate housing
- Remote capacity or extended run-time option
- Fully adjustable lamp-heads
- Water-proof test switch and AC-On indicator
- Wet Location Listed (0°C to 50°C)



- Injection molded, flame retardant thermoplastic housing
- Fully gasketed polycarbonate shield with integral lamp heads
- Dual voltage input 120/277VAC, 60 Hz.
- Maintenance free, sealed lead calcium battery
- UL 924 Listed for wet location



- Fully adjustable lamp-heads
- Single or double lamp-head remote with base-plate



- Fully adjustable lamp-heads
- Single or double lamp-head remote with base
- Fully gasketed for application in wet environment

- * Wet location rated
- * AC-On Indicator and push to test switch



- Durable die-cast aluminum housing
- Fully sealed and gasketed design
- Normally-on and emergency operation
- Includes Self-Diagnostic/Self-Test
- Photo-Control standard and Optional heater



- Housing is fully sealed and gasketed, and has an IP65 rating
- Includes self-diagnostic/self-test feature to monitor proper operation
- Includes photo-sensor and Passive Infra-Red sensor for normally-on operation
- 0°C to 50°C Standard Model, -25°C to 50°C with optional heater



- LED Life-cycle exceeding 10 years
- Quick installation
- Dual-voltage 120 or 277VAC input
- Long-life Nickel Cadmium battery at 3.6VDC for UL recognized 90 minute emergency lighting
- Wet Location Listed for 10°C to 40°C (50°F-104°F)
- External Push-to-Test switch
- Wall or Ceiling Mount



- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Wet Location Listed 0°C to 40°C (32°F to 104°F)
- Includes test switch and AC-On indicator

- Meets international input voltage installation
- Universal single or double face plates



- International Running Man Symbol
- Durable, powder coated 20 gauge steel housing
- Includes face-plates for single or double face
- Includes long-life 4.8VDC Nickel Cadmium battery
- AC, Emergency and Self-Diagnostic models available
- Dual 120/347VAC input, 50/60 Hz



- Meets international input voltage installation
- Molded-in template for Quick Installation
- Universal single or double face SALIDA panel
- Optional long-life 4.8V Nickel Cadmium battery for 90 minute emergency lighting
- Provided with test switch and AC-On indicator



ALERA LIGHTING

ARCHITECTURAL AREA LIGHTING

BEACON PRODUCTS

COLUMBIA LIGHTING

COMPASS

DUAL-LITE

HUBBELL CONTROL SOLUTIONS

HUBBELL INDUSTRIAL LIGHTING

HUBBELL OUTDOOR LIGHTING

KIM LIGHTING

KURT VERSEN

LITECONTROL

PRESCOLITE

WHITEWAY



701 Millennium Blvd. Greenville, SC 29607

Tel 864.678.1000

www.compasslightingproducts.com

COMP0012 01/18

© 2018 *Compass*, a division of Hubbell Lighting, Inc. All rights reserved. Please refer to online specifications for most up-to-date content as specifications are subject to change without notice.