



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH48GEN3060R 4/8 Circuit Emergency PWR PNL/Manual Transfer Swit *Eaton Corp*

Catalog Number	CH48GEN3060R
Manufacturer	Eaton Corp
Description	Eaton Transfer Switch Panel, Standard Manual Transfer Switch, 4 Spaces, 8 Circuits, Nema 3R Enclosure, 5000W, Provisions For Feeder Breakers, to Opposite Phasing
Weight per unit	13.9 (lbs/each)
Product Category	Power Outlet Panel & Pedestal

Features

media	Yes
-------	-----

Dimensions and Weight

Depth	11.2
Height	12.9
Width	4.4

Descriptions

Description	4/8 CIRCUIT EMERGENCY PWR PNL/MANUAL TRANSFER SWIT
extra long description	ETN CH48GEN3060R 4/8 CKT EMERG PWR
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton Transfer switch panel, Standard manual transfer switch, 4 spaces, 8 circuits, NEMA 3R enclosure, 5000W, Provisions for feeder breakers, TO opposite phasing
Product Type	4/8 CKT Emerg PWR PNL/Man Trans Switch

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114511794
Manufacturers Part Number	CH48GEN3060R
UPC	782114511794

Taxonomies, Classifications, and Categories

Category Description	TRANSFER SWITCHES
Type	Transfer switch panel

Packaging

Carton	1
Weight Per each	13.8999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

standard

UL 67,UL 1008