



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG134012FBC21C DG1 480V FR2 N1 7.5HP 12A CT 10HP 16A VT W/ BC Eaton Corp

Catalog Number	DG134012FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input. 5.5 KW, 7.5 HP CT, 3PH, 50/60 HZ, 12A Output, IP21/Type 1 Enclosure, FR2, LCD Display, Internal Emc Filter and DC Choke Ethernet, RS-485
Weight per unit	26.5 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	21.34
Height	14.17
Width	10.24

Descriptions

Description	DG1 480V FR2 N1 7.5HP 12A CT 10HP 16A VT W/ BC
extra long description	ETN DG1-34012FB-C21C DG1,480V FR2 ,
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input. 5.5 kW, 7.5 Hp CT, 3PH, 50/60 Hz, 12A output, IP21/type 1 enclosure, FR2, LCD display, Internal EMC filter and DC choke EtherNet, RS-485
Product Type	DG1, 480V FR2 , N1, 7.5HP, 12A/10HP, 16A, BC

Manufacturer Information

Brand	Eaton
GTIN	00786685878799
Manufacturers Part Number	DG1-34012FB-C21C
UPC	786685878799

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Variable Frequency Drive



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	26.4599

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	IP21/type 1 enclosure UL 508C,EN 61800-5-1,UL Listed,EN 61800-3,EN 62061,cUL Listed,EN ISO 13849-1,IEC 61508,RoHS Compliant,CE Marked,C-Tick Compliant,GoST-R