



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DNF14250MC 16-14AWG Blue ML DSCNT

Panduit Corporation

| | |
|------------------|---|
| Catalog Number | DNF14250MC |
| Manufacturer | Panduit Corporation |
| Description | The Vibration Resistant Male Tab Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In A Blue, Nylon Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 16-14 Awg (1.5-2.5 MM ²). It Is 0.90" (22.9 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Standard Barrel Configuration and An Insulation Grip Sleeve Barrel. It Comes In Bottles Of 100. |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | Nylon |
| Material | Copper |
| Voltage Rating | 600 |
| Wire Size | #14 |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Blue |
| Finish | Nickel-Plated |

Descriptions

| | |
|------------------------|---|
| Description | 16-14AWG BLUE ML DSCNT |
| extra long description | PAN DNF14-250M-C Pan-Term® DNF14-25 |
| Long Description | The vibration resistant male tab disconnect is made of copper and is nickel-plated. It is barrel insulated in a blue, nylon housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 16-14 AWG (1.5-2.5 mm ²). It is 0.90" (22.9 mm) long and 0.25" (6.4 mm) wide. The disconnect has a standard barrel configuration and an insulation grip sleeve barrel. It comes in bottles of 100. |
| Product Type | Pan-Term® DNF14-250M-C Loose Piece Disconnect |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00074983827183 |
| Manufacturers Part Number | DNF14-250M-C |
| UPC | 074983827183 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------|
| Category Description | TERMINALS |
| Type | Disconnect |

Packaging

| | |
|-----------------|-----|
| Carton | 100 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Mounting | 1932-09-01 |
| standard | UL 310 Listed, UL Listed 20H3 E78522; CSA Certified LR31212, C22.2 No.153 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius) |