



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DV14250MBC 16-14 Vinyl Ins Male Disconnect Blue *Panduit Corporation*

Catalog Number	DV14250MBC
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Male Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In Blue Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 16-14 Awg (1.5-2.5 MM ²). It Is 0.96" (24.4 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100.
Weight per unit	1.0 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	#14

Material, Color, and Finish

Color	Blue
Finish	Nickel-Plated

Descriptions

Description	16-14 VINYL INS MALE DISCONNECT BLUE
extra long description	PAN DV14-250MB-C Pan-Term® DV14-250
Long Description	The vibration resistant male disconnect is made of copper and is nickel-plated. It is barrel insulated in blue vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 16-14 AWG (1.5-2.5 mm ²). It is 0.96" (24.4 mm) long and 0.25" (6.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100.
Product Type	Pan-Term® DV14-250MB-C Loose Piece Disconnect



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983822256
Manufacturers Part Number	DV14-250MB-C
UPC	074983822256

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

Packaging

Carton	100
Package	500
Weight Per each	1

Uses, Certifications, and Standards

Mounting standard	1932-09-01 UL 310 Listed, UL Listed 20H3 E78522; CSA Certified LR31212, C22.2 No.153
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)