

Eaton CHP60B225X9

Catalog Number: CHP60B225X9

Eaton CH main breaker loadcenters,PON,Main breaker,225 A,X9,Copper,X9,NEMA 1,Metallic,25 kAIC,CSR,120,60,Three-wire,Single-phase,#2 AWG-300 kcmil,120/240 V

Photo is representative



General specifications

| | |
|----------------------------------|-----------------------------------|
| Product Name | Catalog Number |
| Eaton CH main breaker loadcenter | CHP60B225X9 |
| UPC | Product Length/Depth |
| 786679189672 | 45 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 31 lb | Limited lifetime |
| Certifications | Catalog Notes |
| UL 50 UL 67 | Purchase Size X9 Cover Separately |

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main breaker

Amperage Rating

225 A

Bus material

Copper

Cover

X9

Main circuit breaker

CSR

Number of circuits

120

Number of spaces

60

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Voltage rating

120/240 V

Box size

X9

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP60B225X9

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia