



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHPY44B200X9 CH Pon Loadcenter 200A W Surge

Eaton Corp

Catalog Number	CHPY44B200X9
Manufacturer	Eaton Corp
Description	Eaton CH Surge Loadcenter With Surge Included, Pon, 200 A, Size X9, Copper, Nema 1, 25 Kaic, CSR, 44 SP/88 CKT, Three-Wire, Single-Phase, #2 Awg-300 Kcmil, 120/240 V
Weight per unit	26.0 (lbs/each)
Product Category	Distribution Equipment

### Features

dimensions	46.0000 IN X 15.0000 IN X 4.0000 IN
media	Yes

### Dimensions and Weight

Depth	46
Height	4
Width	15

### Descriptions

Description	CH PON LOADCENTER 200A W SURGE
extra long description	ETN CHPY44B200X9 CH PON Loadcenter,
Features	Eaton's CH 3/4-inch loadcenters enclose CH circuit breakers for power distribution and circuit protection in residential and light commercial applications. Also called a breaker box, electrical box or even a fuse box, the main function is to take electricity supplied by the utility and distribute it throughout the home to feed lights and receptacles. Covers are typically packaged separately and available as surface or flush mount.
Long Description	Eaton CH surge loadcenter with Surge Included, PON,200 A, Size X9,Copper, NEMA 1, 25 kAIC, CSR, 44 sp/88 ckt,Three-wire,Single-phase,#2 AWG-300 kcmil,120/240 V
Product Type	CH Pon Loadcenter, 200A W Surge

### Manufacturer Information

Brand	Eaton
GTIN	00786689728243
Manufacturers Part Number	CHPY44B200X9
UPC	786689728243

### Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
Type	Surge loadcenter



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	26

## Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL 50,UL 67