



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHSPT1ULTRA Singleph- UL1449 3RD Edition- Type 1 SPD SCCR 200K *Eaton Corp*

Catalog Number	CHSPT1ULTRA
Manufacturer	Eaton Corp
Description	Eaton SPD CHSP Service Entrance Surge Protection, Type 1, 50KA One Time Surge Current Rating, Single-Phase
Weight per unit	1.0 (lbs/each)
Product Category	Surge Suprsr-Prot Dev-LN Condi

Features

Phase	1
Voltage Rating	120/240 V

Dimensions and Weight

Depth	1
Height	1
Width	1

Descriptions

Description	SINGLEPH- UL1449 3RD EDITION- TYPE 1 SPD SCCR 200K
extra long description	ETN CHSPT1ULTRA 1PH UL1449 3RD ED T
Features	Eaton offers a comprehensive family of surge products for use at service entrances. These products can help protect sensitive electronics against the damaging effects of surges. Due to the evolution of electronics and microprocessors in the home, there is a continuous challenge to provide quality (clean) power for electronic loads such as appliances, computers/home office and entertainment systems. Surges caused by lightning, utility grid switching and other sources travel on current carrying conductors t
Long Description	Eaton SPD CHSP Service Entrance Surge Protection, Type 1, 50kA one time surge current rating, Single-phase
Product Type	1PH UL1449 3RD Ed Type 1 SPD SCCR 200ka

Manufacturer Information

Brand	Eaton
GTIN	00786685436821
Manufacturers Part Number	CHSPT1ULTRA
UPC	786685436821

Taxonomies, Classifications, and Categories

Category Description	SURGE SUPRESSION PRODUCTS
Type	Plug on module surge protection device



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 1449