



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DWZ200B 2CHAN 7DAY Astronomic Time Clock

Nsi Industries

Catalog Number	DWZ200B
Manufacturer	Nsi Industries
Description	356 Day Astro Digital Timer 2CH Title 24
Weight per unit	2.4 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Screw
Contact Rating	120-208-240-277
Phase	Single Phase
Poles	1
Timing Range	365 Day-7 Day Advanced

Dimensions and Weight

Size	L=5.000 - H=9.125 - W=4.500
------	-----------------------------

Descriptions

Description	2CHAN 7DAY ASTRONOMIC TIME CLOCK
extra long description	TORK DWZ200B 356 Day Astro Digital
Features	Tork 7/365 Day 2 Channel SPDT Astronomic Time Switch APPLICATIONS: Outdoor Lighting Security Lighting Parking Lot Lighting Canopy Lighting FEATURES: INPUT VOLTAGE: 120/208-240/277 50/60Hz DRY CONTACTS: SPDT NO. OF CHANNELS: 1 Channel SCHEDULING: 99 ON/OFF set points allow individual programs for each day of the week at a minimum 1 minute apart. SunSet ASTRONOMIC: Adjusts daily to changes in sunset times. Adjustable 10 - 60 degrees Northern or Southern latitudes. Can be individually offset +/- 1 to 240 minu
Long Description	356 Day Astro Digital Timer 2CH Title 24
Product Type	356 Day Astro Digital Timer 2CH Title 24
Special Features	99 On-Off Set Points - Astronomic Time Switch With Holiday Schedule And Manual Override

Manufacturer Information

Brand	NSi
GTIN	00786261820983
Manufacturers Part Number	DWZ200B
UPC	786261820983



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	365 Day-7 Day Advanced - 1 Or 2 Channel

Packaging

Carton	1
Weight Per each	2.4

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 3R Noryl Indoor-Outdoor
environmental conditions	-40 to + 158
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	-40 to + 158
standard	cULus