



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CSB20AC3I 20A 120/277VAC B+S Wire Comm 3W SW Iv *Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | CSB20AC3I  |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Construction 3-Way Switch, Back and Side-Wire, 20A 120/277V. These Switches Offer Excellent Value While Meeting Federal Specification Standards. External Screw-Pressure-Plate Back Wiring Enables Fast Installation and Superior Electrical Connections. Rugged Construction Shrugs Off Hard Use and Abuse. |
| Weight per unit  | 0.1893 (lbs/each)  |
| Product Category | Gen Purpose Switches   |

### Features

|                       |  |
|-----------------------|--|
| action                | Three pole                                 |
| amperage rating       | 20   |
| connection            | Side Wire or external screw-pressure plate |
| Connection Type       | Wired                                      |
| Contact Configuration | One piece brass alloy contact arm          |
| Contact Rating        | Oversized silver alloy contacts            |
| Degree of Protection  | 1500V Dielectric Withstand Voltage         |
| indoor/outdoor        | Indoor                                     |
| insulation            | False                                      |
| Material              | Thermoplastic                              |
| Poles                 | 3-way                                      |
| Switch Type           | Toggle                                     |
| Voltage               | 120/277 V                                  |
| Voltage Rating        | 120/277                                    |
| Wire Size             | #14 - #10 Awg                              |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | Matte |
|--------|-------|

### Dimensions and Weight

|      |        |
|------|--------|
| Size | 3.3 in |
|------|--------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 20A 120/277VAC B+S WIRE COMM 3W SW IV  |
| extra long description | P&S CSB20AC3I 20A 120/277VAC B+S WI  |
| Long Description       | Construction 3-Way Switch, Back and Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse. |
| Product Type           | 20A 120/277VAC B+S Wire Comm 3W SW I   |
| Special Features       | Back & side wire, locking support, heavy duty toggle   |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007126273   |
| Manufacturers Part Number | CSB20AC3-I       |
| UPC                       | 785007126273     |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type                 | SWITCH                 |

## Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 10     |
| Package         | 50     |
| Weight Per each | 0.1893 |

## Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | Commercial  |
| Enclosure   | Nylon   |
| Mounting    | WALL  |
| nema rating | WD-1 and WD-6   |
| standard    | FEDSPEC, CULUS, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC |