



20" PLASTIC ENCLOSURE WITH HINGED DOOR

ENP2050 | [On-Q](#)

FEATURES & BENEFITS

Constructed with a robust, wireless transparent ABS plastic material, this lightweight enclosure is designed to integrate wireless devices into traditional structured wiring installations.

The enclosure mounts easily for both surface and recessed applications, and hinged door is equipped with extra venting along the vertical plane for superior heat dissipation. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Cover adds 1.2" of depth for cable headroom and 3rd party device compatibility.
- Universal mounting grid maximizes compatibility with 3rd party products without additional brackets.
- Extra venting along the vertical plane of the door allows for superior heat dissipation.
- Staggered mounting tabs allow multiple enclosures to mount in adjacent stud bays.
- Cover is reversible with metal hinge that can attach to left or right side of enclosure.
- Lockable with provided screws
- Tapered design allows enclosures and covers to stack for efficient transportation and warehousing
- Hinged door covers drywall hole for clean finish
- UL listed.

SPECIFICATIONS

GENERAL INFO

Color: White (Paintable)*
Type: Enclosure

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including

Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems

UL Standard: Yes

CONSTRUCTION INFORMATION

Material 1: ABS Plastic

DIMENSIONS

Depth (Metric): 159.6 mm

Depth (US): 6.28"

Height (Metric): 552.9mm

Height (US): 21.77"

Width (Metric): 434.3mm

Width (US): 17.1"

Primary Packaging Weight (Metric): 2.95 kg

Product Weight (Metric): 2.04 kg

Product Weight (US): 4.5 lbs

TECHNICAL INFORMATION

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C