


**ALL-PRO™****ET400LV****4" NON-IC LOW VOLTAGE HOUSING**

- For non-insulated ceilings or where insulation can be kept 3" from housing (U.S. only)

**DESCRIPTION**

Small aperture low voltage housing for accent and task lighting.

**Housing Features**

- Integral thermal protector guards against misuse of insulation materials and improper lamping.
- Integral magnetic transformer steps line voltage down to lamp operating voltage.
- Junction Box is listed for through branch circuit wiring and has three 1/2" knockouts and four non metallic (NM) sheathed cable knockouts with true pry out slots. NM sheathed cable pryouts include built in strain relief and require no additional clamps.
- Pre-installed, captive bar hangers

allow housing to be positioned at any point within a 24" joist span. Score lines provided for easy field shortening for 12" joists.



- Unique arrowhead design provides "Rapid" installation.
- Bar hangers can be repositioned 90° without tools on plaster frame.
- Hangers fit onto T-Bar spline for quick alignment and can be permanently secured with optional TB7 T-Bar clip.
- 120V magnetic transformer for lamps up to 50W.

**Installation Features**

- 5 1/2" Height allows use in 2" x 6" joist construction.
- Housing can be removed from plaster frame for junction box access.
- Housing can be adjusted in plaster frame for ceilings up to 1" thick.

**Listings**

- UL Damp Location
- UL Feed Through
- CSA Certified
- IP Rated

**ET400LVR****4" NON-IC LOW VOLTAGE REMODEL HOUSING**

- For non-insulated ceilings or where insulation can be kept 3" from housing
- Can be installed from below the ceiling

The ET400LVR is a low voltage fixture designed for small aperture trims.

**Housing Features**

- Integral magnetic transformer steps line voltage down to 12V lamp operating voltage.
- Junction box is listed for through branch circuit wiring and has four 1/2" knockouts and four Non metallic (NM) sheathed cable knockouts with true pry-out slots.



- ET400LVR can be slipped through ceiling opening.
- Four remodel clips secure housing and accommodate 1/2" and 5/8" ceiling thickness.
- 120V magnetic transformer for lamps up to 50W.


**Installation Features**

- 5 1/2" height allows use in 2" x 6" joist construction.

**Listings**

- UL Damp Location
- UL Feed Through
- CSA Certified



**ALL-PRO™****ET400LV****4" NON-IC LOW VOLTAGE HOUSING**

- For non-insulated ceilings or where insulation can be kept 3" from housing (U.S. only)

**DESCRIPTION**

Small aperture low voltage housing for accent and task lighting.

**Housing Features**

- Integral thermal protector guards against misuse of insulation materials and improper lamping.
- Integral magnetic transformer steps line voltage down to lamp operating voltage.
- Junction Box is listed for through branch circuit wiring and has three 1/2" knockouts and four non-metallic (NM) sheathed cable knockouts with true pry out slots. NM sheathed cable pryouts include built in strain relief and require no additional clamps.
- Pre-installed, captive bar hangers

allow housing to be positioned at any point within a 24" joist span. Score lines provided for easy field shortening for 12" joists.



- Unique arrowhead design provides "Rapid" installation.
- Bar hangers can be repositioned 90° without tools on plaster frame.
- Hangers fit onto T-Bar spline for quick alignment and can be permanently secured with optional TB7 T-Bar clip.
- 120V magnetic transformer for lamps up to 50W.

**Installation Features**

- 5 1/2" Height allows use in 2" x 6" joist construction.
- Housing can be removed from plaster frame for junction box access.
- Housing can be adjusted in plaster frame for ceilings up to 1" thick.

**Listings**

- UL Damp Location
- UL Feed Through
- CSA Certified
- IP Rated

**ET400LVR****4" NON-IC LOW VOLTAGE REMODEL HOUSING**

- For non-insulated ceilings or where insulation can be kept 3" from housing
- Can be installed from below the ceiling

The ET400LVR is a low voltage fixture designed for small aperture trims.

**Housing Features**

- Integral magnetic transformer steps line voltage down to 12V lamp operating voltage.
- Junction box is listed for through branch circuit wiring and has four 1/2" knockouts and four Non-metallic (NM) sheathed cable knockouts with true pry-out slots.

- ET400LVR can be slipped through ceiling opening.
- Four remodel clips secure housing and accommodate 1/2" and 5/8" ceiling thickness.
- 120V magnetic transformer for lamps up to 50W.

**Installation Features**

- 5 1/2" height allows use in 2" x 6" joist construction.

**Listings**

- UL Damp Location
- UL Feed Through
- CSA Certified

