




GE
Lighting

10204 - F18T12/CW/HO

GE Cool White T12



CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Lamp Mortality



Graphs_Spectral Power Distribution



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T12
Base	Recessed Double Contact (R17d)
Rated Life (NOM)	9000.0 h
Bulb Material	Soda lime
Starting Temperature (MIN)	-29.0 °C
Mercury Content (NOM)	9.0 mg
Picograms of Mercury (NOM)	1333.3 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	1000.0
Mean Lumens (NOM)	750.0
Nominal Initial Lumens per Watt (NOM)	33.33333
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	60.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	30.0
Cathode Resistance Ratio - Rh/ Rc (MIN)	4.25
Cathode Resistance Ratio - Rh/ Rc (MAX)	6.5
Current Crest Factor (MAX)	1.7

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	18.000 in(457.2 mm)
Nominal Length (NOM)	18.000 in(457.2 mm)
Bulb Diameter (DIA) (NOM)	1.500 in(38.1 mm)

PRODUCT INFORMATION


Product Code	10204
Description	F18T12/CW/HO
Standard Package	Case
Standard Package GTIN	10043168102046
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard	24
Package	
UPC	043168102049



GE
Lighting

10204 - F18T12/CW/HO

GE Cool White T12



CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
 - Wear safety glasses and gloves when handling lamp.
 - Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Lamp Mortality



Graphs_Spectral Power Distribution



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T12
Base	Recessed Double Contact (R17d)
Rated Life (NOM)	9000.0 h
Bulb Material	Soda lime
Starting Temperature (MIN)	-29.0 °C
Mercury Content (NOM)	9.0 mg
Picograms of Mercury (NOM)	1333.3 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	1000.0
Mean Lumens (NOM)	750.0
Nominal Initial Lumens per Watt (NOM)	33.33333
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	60.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	30.0
Cathode Resistance Ratio - Rh/ Rc (MIN)	4.25
Cathode Resistance Ratio - Rh/ Rc (MAX)	6.5
Current Crest Factor (MAX)	1.7

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	18.000 in(457.2 mm)
Nominal Length (NOM)	18.000 in(457.2 mm)
Bulb Diameter (DIA) (NOM)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	10204
Description	F18T12/CW/HO
Standard Package	Case
Standard Package GTIN	10043168102046
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard	24
Package	
UPC	043168102049