



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F1X1LG6 1" X 1" Narrow Slot LT Gray Duct

Panduit Corporation

Catalog Number	F1X1LG6
Manufacturer	Panduit Corporation
Description	The F1X1LG6 Panduct Lead-Free PVC Narrow Slot Wiring Duct Features A Narrow Slot/Finger Design That Closely Matches The Spacing Of High-Density Components. Upper and Lower Scorelines Allow For Easy Finger/Sidewall Section Removal. UI 94 Flame Class Of V-0 With A UI Recognized Continuous-Use Temperature Up To 122°F (50°C). Mounting Holes Provided. Lead-Free PVC. 1" X 1" (25.4 MM X 25.4 MM) and 6' (1.83 M) Long. Cover Sold Separately. Color Light Gray.
Weight per unit	1.0 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

connection	Mounting Holes
media	Yes

Dimensions and Weight

Height	1.13
Length	NA
Size	1.00 x 1.00

Descriptions

Description	1" X 1" NARROW SLOT LT GRAY DUCT
extra long description	PAN F1X1LG6 Panduct® F1X1LG6 Base W
Long Description	The F1X1LG6 Panduct Lead-Free PVC Narrow Slot Wiring Duct features a narrow slot/finger design that closely matches the spacing of high-density components. Upper and lower scorelines allow for easy finger/sidewall section removal. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. Lead-free PVC. 1" x 1" (25.4 mm x 25.4 mm) and 6' (1.83 m) long. Cover sold separately. Color Light Gray.
Product Type	Panduct® F1X1LG6 Base Wiring Duct

Manufacturer Information

Brand	PANDUIT
GTIN	00074983375035
Manufacturers Part Number	F1X1LG6
UPC	074983375035

Taxonomies, Classifications, and Categories

Category Description	WIRE DUCT AND COVERS
----------------------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 120

Weight Per foot 1