



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DNF14250MC Pan-Term® DNF14-250M-C Lo Panduit Corporation

Catalog Number	DNF14250MC
Manufacturer	Panduit Corporation
Description	Male Disconnect, Standard Barrel, Insulation Grip Sleeve, Funnel Entry Type; Blue Color; 16 Awg Min. Conductor Size; 14 Awg Max. Conductor Size; UI, Csa Approval; 221 Deg F Temperature Rating; 100 Standard Package; Nylon Barrel Insulated Insulation Type
Weight per unit	0.3000 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Insulation Type	Nylon Barrel Insulated
Maximum Conductor Size	14 AWG
Minimum Conductor Size	16 AWG
Tab Size	0.25 INCH X 0.032 INCH

Material, Color, and Finish

Color	Blue
-------	------

Descriptions

Additional Information	RoHS Compliant; Overall Dimension 0.9 Inch Length x 0.25 Inch Width; Wire Strip Length 9/32 Inch; Voltage Rating 600 Volt; Base Material Nickel Plated Copper
Commodity Description	SMALL TERMINALS & CONNECTORS
Description	PAN-TERM® DNF14-250M-C LO
extra long description	STANDARD BARREL, INSULATION GRIP SLEEVE, FUNNEL ENTRY TYPE; BLUE COLOR; 16 AWG MIN. CONDUCTOR SIZE; 14 AWG MAX. CONDUCTOR SIZE; UL, CSA APPROVAL; 221 DEG F TEMPERATURE RATING; 100 STANDARD PACKAGE; NYLON BARREL INSULATED INSULATION TYPE; 0.25 INCH X 0.032 INCH TAB SIZE; PAN-TERM[R] BRAND; ROHS COMPLIANT; OVERALL DIMENSION 0.9 INCH LENGTH X 0.25 INCH WIDTH; WIRE STRIP LENGTH 9/32 INCH; VOLTAGE RATING 600 VOLT; BASE MATERIAL NICKEL PLATED COPPER; DNF-M MODEL
Long Description	MALE DISCONNECT, STANDARD BARREL, INSULATION GRIP SLEEVE, FUNNEL ENTRY TYPE; BLUE COLOR; 16 AWG MIN. CONDUCTOR SIZE; 14 AWG MAX. CONDUCTOR SIZE; UL, CSA APPROVAL; 221 DEG F TEMPERATURE RATING; 100 STANDARD PACKAGE; NYLON BARREL INSULATED INSULATION TYPE
Product Type	Male Disconnect



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983827183
Manufacturers Part Number	DNF14-250M-C
Model	DNF-M
UPC	074983827183

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Standard Barrel, Insulation Grip Sleeve, Funnel Entry

Packaging

Carton	100
Package	1000
Standard Package	100 W
Weight Per each	0.3

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	221 DEG F