



GE  
Lighting

**63547 - F32T8/835/PRO/EC**

F32T8/835/PRO/EC



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	20000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	53.64612 pg
Primary Application	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2925.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	85.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	32.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	63547
Description	F32T8/835/PRO/EC
Standard Package	00-Case
Standard Package GTIN	10043168635476
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168635479



GE  
Lighting

**63547 - F32T8/835/PRO/EC**

F32T8/835/PRO/EC



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Medium Bi-Pin (G13)
Bulb Material	20000.0 h
Starting Temperature (MIN)	Sodalime glass
Mercury Content (NOM)	10.0 °C
Picograms of Mercury (NOM)	2.95 mg
Primary Application	53.64612 pg
	Full Wattage

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	2925.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	85.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	32.0
---------------	------

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

**PRODUCT INFORMATION**

Product Code	63547
Description	F32T8/835/PRO/EC
Standard Package	00-Case
Standard Package GTIN	10043168635476
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168635479