



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DV18250MBCY 18-22AWG Red Insld ML Tab DSCNCT *Panduit Corporation*

Catalog Number	DV18250MBCY
Manufacturer	Panduit Corporation
Description	The Vibration Resistant Male Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In Red Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 22-18 Awg (0.5-1.0 MM ²). It Is 0.98" (24.9 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100.
Weight per unit	0.3100 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel Entry
insulation	Vinyl
Material	Copper
Voltage Rating	600
Wire Size	#18

Material, Color, and Finish

Color	Red
Finish	Nickel Plated

Descriptions

Description	18-22AWG RED INSLTD ML TAB DSCNCT
extra long description	PAN DV18-250MB-CY Pan-Term® DV18-25
Long Description	The vibration resistant male disconnect is made of copper and is nickel-plated. It is barrel insulated in red vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 22-18 AWG (0.5-1.0 mm ²). It is 0.98" (24.9 mm) long and 0.25" (6.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100.
Product Type	Pan-Term® DV18-250MB-Cy Loose Piece Disconnect

Manufacturer Information

Brand	Panduit®
GTIN	00074983685622
Manufacturers Part Number	DV18-250MB-CY
UPC	074983685622



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Disconnect

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.31

Uses, Certifications, and Standards

Mounting	1932-09-01
standard	CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed 20H3 E78522
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)