



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50DM1 E50 Heavy Duty Limit Switch

Eaton Corp

Catalog Number	E50DM1
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Head, Side Rotary, Two Pos, Maintained, 50 Degrees to Operate Contacts, 14-250F(-10-121C), Screw Term, Nema 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Diec ZN, UI, Csa, Ce
Weight per unit	0.1100 (lbs/each)
Product Category	Limit Switch Heads

Features

dimensions	1.0500 IN X 1.5400 IN X 2.4600 IN
Material	Die Cast Zinc

Dimensions and Weight

Depth	1.54
Height	2.46
Width	1.54

Descriptions

Description	E50 HEAVY DUTY LIMIT SWITCH
extra long description	ETN E50DM1 E50 LS HEAD,SIDE R 2POS,
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Head,Side Rotary,Two Pos,Maintained,50 degrees to operate contacts,14-250F(-10-121C),Screw term,NEMA 1,3,3S,4,4X,6,6P,13,IP67,Diec Zn,UL,CSA,CE
Product Type	E50 LS Head, Side R 2POS, Low F, Spring RTN

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290584
Manufacturers Part Number	E50DM1
UPC	782113290584

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - Other Stationary Mach Equip In Factory - Machine Tools: Cutting Stationary Mach Equip In Factory - Machine Tools: Forming Ind Facilities & Factories - Industrial Facilities/Factories - Other
Operating Temperature standard	14 UL Recognized, CSA Certified, UL Listed, RoHS Compliant, CE Marked