



E50NN1 E50 Heavy Duty Limit Switch_Special Purpose

Eaton Corp

Catalog Number	E50NN1
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Side Rotary, Neut Position, 5 Deg Travel, 14-200F(-10-94C), 2NO-2NC, 10A@240VAC, 1A@250VDC, Mech 10M Elec 100K Cy Full Load, 8000 Cy/HR, Screw Term, 1/2NPT Cond, Nema 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Diec ZN, UL, CSA, Ce
Weight per unit	0.4100 (lbs/each)
Product Category	Heavy Duty Limit Switches

Descriptions

Description	E50 HEAVY DUTY LIMIT SWITCH_SPECIAL PURPOSE
extra long description	ETN E50NN1 LIMIT SWITCH,1NO/1NC,SID
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch, Side Rotary, Neut Position, 5 deg travel, 14-200F(-10-94C), 2NO-2NC, 10A@240Vac, 1A@250Vdc, Mech 10M Elec 100k cy full load, 8000 cy/hr, Screw term, 1/2NPT cond, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Diec Zn, UL, CSA, CE
Product Type	Limit Switch, 1NO/1NC, Side Rot, Neutr

Manufacturer Information

Brand	Eaton
GTIN	00782113290706
Manufacturers Part Number	E50NN1
UPC	782113290706

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
----------------------	----------------

Packaging

Carton	1
Weight Per each	0.41