

Eaton FAZ-C50/2-NA

Catalog Number: FAZ-C50/2-NA

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,50 A,10 kAIC,Two-pole,240 V,5-10X /n,50-60 Hz,Screw terminals,C Curve



General specifications

| | |
|----------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton FAZ branch protector | FAZ-C50/2-NA |
| UPC | Product Length/Depth |
| 786689042387 | 1.4 in |
| Product Height | Product Width |
| 1.5 in | 3 in |
| Product Weight | Warranty |
| 0.5 lb | 1 year |
| Certifications | |
| UL 489 | |

Physical Attributes

Number of poles

Two-pole

Terminals

Screw

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/2-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton FAZ-C50/2-NA

Catalog Number: FAZ-C50/2-NA

Eaton FAZ branch protector,UL 489 Industrial miniature circuit breaker - supplementary protector,Medium levels of inrush current are expected,50 A,10 kAIC,Two-pole,240 V,5-10X /n,50-60 Hz,Screw terminals,C Curve



General specifications

| | |
|----------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton FAZ branch protector | FAZ-C50/2-NA |
| UPC | Product Length/Depth |
| 786689042387 | 1.4 in |
| Product Height | Product Width |
| 1.5 in | 3 in |
| Product Weight | Warranty |
| 0.5 lb | 1 year |
| Certifications | |
| UL 489 | |

Physical Attributes

Number of poles

Two-pole

Terminals

Screw

Type

UL 489 Industrial miniature circuit breaker - supplementary protector

Performance Ratings

Amperage Rating

50 A

Circuit protection

C curve

Frequency rating

50-60 Hz

Interrupt rating

10 kAIC

Trip Type

5-10X /n

Voltage rating

277/480V

Miscellaneous

Application

Suitable for applications where medium levels of inrush current are expected

Resources

Catalogs

[UL 489 DIN rail miniature circuit breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - FAZ-C50/2-NA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)