



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECD18 1/2" Drain & Breather

Crouse-Hinds

Catalog Number	ECD18
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Ecd Combination Breather/Drain, Stainless Steel With Neoprene Tube, 1/2"
Weight per unit	0.2300 (lbs/each)
Product Category	Sealing Bodies

Features

dimensions	1.0200 IN X 0.8800 IN X 3.1000 IN
Material	Stainless Steel

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Description	1/2" DRAIN & BREATHER
extra long description	CRS-H ECD18 1/2 COMBINATION DRAIN/B
Features	Crouse-Hinds series ECD breathers and drains are for use in hazardous location conduit systems to drain accumulated condensate and provide ventilation to minimize condensation. A breather is installed in the top of an enclosure or in the upper section of a conduit system. A standard drain is installed in the bottom of an enclosure or in the lower section of a conduit system. At least one breather should be used with each drain. ECDs are also available in universal and combination models. A universal E
Long Description	Eaton Crouse-Hinds series ECD combination breather/drain, Stainless steel with neoprene tube, 1/2"
Product Type	1/2 Combination Drain/Breather

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274275017
Manufacturers Part Number	ECD18
UPC	782274275017

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	COMBINATION BREATHER/DRAIN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	5
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Class I Div 1 2 Group B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2