



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



G4X4LG6 SLTD Wiring Duct *Panduit Corporation*

Catalog Number	G4X4LG6
Manufacturer	Panduit Corporation
Description	The G4X4LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct Feature A Wide Slot/Finger Design That Provides Greater Sidewall Rigidity and Is Suitable With A Range Of Wire Bundle Sizes. UL 94 Flame Class Of V-0 With A UL Recognized Continuous-Use Temperature Up to 122°F (50°C). Mounting Holes Provided. 4.0" X 4.0" (101.6 MM X 101.6 MM) and 6' (1.8 M) Long. Cover Sold Separately. Color Light Gray.
Weight per unit	0.0662 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

connection	Mounting Holes
media	Yes

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Length	NA
Size	4.25 x 4.10
Width	4.25

Descriptions

Description	SLTD WIRING DUCT
extra long description	PAN G4X4LG6 Panduct® G4X4LG6 Base W
Long Description	The G4X4LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct feature a wide slot/finger design that provides greater sidewall rigidity and is suitable with a range of wire bundle sizes. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. 4.0" x 4.0" (101.6 mm x 101.6 mm) and 6' (1.8 m) long. Cover sold separately. Color Light Gray.
Product Type	Panduct® G4X4LG6 Base Wiring Duct

Manufacturer Information

Brand	PANDUIT
GTIN	00074983545933
Manufacturers Part Number	G4X4LG6
UPC	074983545933



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description WIRE DUCT AND COVERS

Type Base Wiring Duct

Packaging

Carton 60

Weight Per each 0.0662

Uses, Certifications, and Standards

Application Wide slot/finger design provides greater sidewall rigidity and can
..... be used in a wide range of applications

standard CSA Approved;RoHS Compliant, UL Recognized, CE Compliant