



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GASK805N 1-1/2 Neo Body GS

Crouse-Hinds

Catalog Number	GASK805N
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 8 Gasket, Neoprene, 1-1/2", Open
Weight per unit	0.0400 (lbs/each)
Product Category	Bodies & Covers

Features

connection	Water Jet Cut
dimensions	2.8100 IN X 0.0600 IN X 7.9400 IN
Material	Neoprene

Material, Color, and Finish

Color	Black
Finish	Black

Descriptions

Description	1-1/2 NEO BODY GS
extra long description	CRS-H GASK805N 1 1/2 OPEN NEO FORM
Features	One hundred years after the introduction of the Condulet, Eaton remains the leader in conduit outlet bodies with its Crouse-Hinds series. The line has grown to six families manufactured in a variety of materials, and Form 8 bodies are offered in seven different shapes to provide the most flexible offering on the market. Form 8 Condulet outlet bodies provide more room for heavier conductors. Many shapes and sizes are available for rigid threaded conduit. Two cover screws on all body sizes provide tight
Long Description	Eaton Crouse-Hinds series Condulet Form 8 gasket, Neoprene, 1-1/2", Open
Product Type	1 1/2 Open Neo Form 8 Gask

Manufacturer Information

Brand	Eaton
GTIN	00782274098586
Manufacturers Part Number	GASK805N
UPC	782274098586

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Gasket



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Package	25
---------	----

Weight Per each	0.04
-----------------	------

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
-------------	----------------------------------------------------------------------

standard	UL 514B, CSA C22.2
----------	--------------------