



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GFR5362SG 20A 125V Ind Tamper ST Gfci, Brown *Hubbell Wiring Devices*

Catalog Number	GFR5362SG
Manufacturer	Hubbell Wiring Devices
Description	Power Protection Products, Receptacle, Gfci, Industrial Grade, Safetygrade Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown
Weight per unit	0.5500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and Side Wired Terminal Screws
Material	Thermoplastic
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wattage	2,000
Wire Size	#14 AWG to #12 AWG

### Material, Color, and Finish

Color	Brown
-------	-------

### Dimensions and Weight

Size	Standard Sized
------	----------------

### Descriptions

Description	20A 125V IND TAMPER ST GFCI, BROWN
extra long description	HCI GFR5362SG 20A/125V INDL. TAMPER
Long Description	Power Protection Products, Receptacle, GFCI, Industrial Grade, SafetyGrade Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown
Product Type	20A/125V Indl. Tamper ST Gfci, Brown
Special Features	Self Test Feature

### Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585440941
Manufacturers Part Number	GFR5362SG
sub brand	Straight Blade GFCI Receptacles
UPC	783585440941



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	DECORATOR DUPLEX

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	0.55

## Uses, Certifications, and Standards

Application	Extra Heavy Duty with Self Test
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	NEMA WD1 and WD5, UL 498 and 943