



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHQ1020 20A 277 Volt 14 Ka *Eaton Corp*

Catalog Number	GHQ1020
Manufacturer	Eaton Corp
Description	Eaton GHQ Thermal Magnetic Circuit Breaker, Thermal-Magnetic Circuit Breaker, 20 A, 14 Kaic, Single-Pole, 277 V, Non-Interchangeable, GHP, GDB-Frame, 120/208/240 V Shunt Trip
Weight per unit	0.3500 (lbs/each)
Product Category	1 Pole

Features

dimensions	2.9000 IN X 1.0000 IN X 2.9000 IN
interrupt rating	14 kAIC
Poles	1
Trip Type	Non-Interchangeable
Voltage Rating	277V

Descriptions

Description	20A 277 VOLT 14 KA
extra long description	ETN GHQ1020 20 Amp 277 Volt 14 Ka
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton GHQ thermal magnetic circuit breaker, Thermal-magnetic circuit breaker, 20 A, 14 kAIC, Single-pole, 277 V, Non-Interchangeable, GHP, GDB-Frame, 120/208/240 V Shunt trip
Product Type	20 Amp 277 Volt 14 Ka

Manufacturer Information

Brand	Eaton
GTIN	00782114985113
Manufacturers Part Number	GHQ1020
UPC	782114985113

Taxonomies, Classifications, and Categories

Type	Thermal magnetic circuit breakers
------	-----------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	24
Weight Per each	0.35

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 489