



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL1221L SP Tog, Ind GRD, 20A 120/277V, Lock

*Hubbell Wiring Devices*

Catalog Number	HBL1221L
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Locking Toggle Switches, General Purpose Ac, Single Pole, 20A 120/277V Ac, Back and Side Wired, Black Key Guide
Weight per unit	0.0780 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Snap
actuator	Double Ended Key
amperage rating	20
connection	Terminal Screws
Contact Configuration	2-Position
Contact Rating	Full Rated
Current Rating	20
indicator	Dot Indicates On
load	Inductive or Resistive
Material	COMPOSITE
pallet quantity	4050
Voltage Rating	120-277 VAC
Wattage	5540

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Size	4.06 in x 1.31 in x 1.13 in
------	-----------------------------

### Descriptions

Description	SP TOG, IND GRD, 20A 120/277V, LOCK
extra long description	HWDK HBL1221L SP TOG, IND GRD, 20A
Long Description	Switches and Lighting Controls, Extra Heavy Duty Industrial Grade, Locking Toggle Switches, General Purpose AC, Single Pole, 20A 120/277V AC, Back and Side Wired, Black Key Guide
Product Type	SP Tog, Ind GRD, 20A 120/277V, Lock
Special Features	Standard Product



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585431444
Manufacturers Part Number	HBL1221L
series	Extra Heavy Duty
UPC	783585431444

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	LOCKING

## Packaging

Carton	1
Package	10
Weight Per each	0.078

## Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
Mounting	Mounting Screws
standard	UL Listed
Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact