




GE
Lighting

68871 - F96T8/XL/SPX50/2
F96T8/XL/SPX50/2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Single Pin (Fa8)
Bulb Material	24000.0 h
Starting Temperature (MIN)	Sodalime glass
Mercury Content (NOM)	10.0 °C
Picograms of Mercury (NOM)	90.0 mg
Primary Application	663.7168 pg
	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	5950.0
Mean Lumens (NOM)	5650.0
Nominal Initial Lumens per Watt (NOM)	100.8475
Color Temperature (NOM)	5000.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	59.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	96.000 in(2438.4 mm)
Nominal Length (NOM)	96.000 in(2438.4 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	68871
Description	F96T8/XL/SPX50/2
Standard Package	Case
Standard Package GTIN	10043168688717
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
UPC	043168688710