



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FD1020 FD BRKR 1 Pole 20AMP With Load Only Terms

*Eaton Corp*

Catalog Number	FD1020
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Single-Pole, 20 A, 347 Vac, 125 VDC, Load Side, 50/60 HZ
Weight per unit	1.6 (lbs/each)
Product Category	1 Pole

### Features

Current Rating	20 A
dimensions	3.3800 IN X 1.3800 IN X 6.0000 IN
media	Yes
Poles	1
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	347 Vac, 125 Vdc

### Descriptions

Description	FD BRKR 1 POLE 20AMP WITH LOAD ONLY TERMS
extra long description	ETN FD1020 FD BRK 1P 20A WITH LOAD
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Single-pole, 20 A, 347 Vac, 125 Vdc, Load side, 50/60 Hz
Product Type	FD BRK 1P 20A With Load Only Terminals

### Manufacturer Information

Brand	Eaton
GTIN	00786679312117
Manufacturers Part Number	FD1020
UPC	786679312117

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	1.6

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed