




GE
Lighting

74198 - FLE13HT3/2/SW/BX

GE energy smart® spiral® CFL 13 watt T3 spiral 1-pack

- Use original GE's Soft White when you need a light without glare and harsh shadows.
- Saves \$37.00 in energy costs*
- Lasts 8 times longer than a 60 watt regular soft white bulb*
- \$51 in energy savings over the life of the bulb based on 3 hours per day usage
- 60 watt replacement uses only 13 watts
- Energy Star Qualified
- Estimated yearly energy costs \$1.57 based on 3 hours per day \$0.11 per kWh
- Lasts 9.1 years based on 3 hours per day usage
- Save money and save energy with GE energy smart® spiral® CFL bulbs. GE energy smart® bulbs use 75% less energy than standard incandescents, helping you save money on energy. And, because they last 8 times longer than a standard incandescent, you'll replace these bulbs less often. Use general purpose GE energy smart® spiral® CFL bulbs in common household fixtures like table lamps, floor lamps and bare lamp sockets
- T3 spiral shape with medium base for use in table lamps and enclosed fixtures
- Estimated yearly energy costs \$1.57 based on 3 hours per day \$0.11 per kWh

a product of
ecomagination



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Remove and install by grasping only plastic portion of the lamp.

Warning

- Risk of Electric Shock
 - Do not open - no user serviceable parts inside.
 - Do not use where directly exposed to water.

NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.

GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	Medium Screw (E26)
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	8000.0 h
Starting Temperature (MIN)	-15.0 °C
Total Harmonic Distortion (THD) (NOM)	120.0 %
Life in Years (NOM)	9.1
Mercury Content (NOM)	3.0 mg
Picograms of Mercury (NOM)	568.2 pg
Primary Application	Standard;Facilities;Retail Display;Hospitality;Office;Restaurant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	825.0
Mean Lumens (NOM)	660.0
Nominal Initial Lumens per Watt (NOM)	63.46154
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	13.0
Input Voltage (NOM)	120.0 V
Estimated Energy Cost per Year (NOM)	1.57
Input Current (NOM)	0.18 A
Power Factor (NOM)	0.6

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	4.900 in(124.5 mm)
Nominal Length (NOM)	4.700 in(119.4 mm)

PRODUCT INFORMATION

Product Code	74198
Description	FLE13HT3/2/SW/BX
Standard Package	Case
Standard Package GTIN	10043168741986
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168741989



GE
Lighting

74198 - FLE13HT3/2/SW/BX


GE energy smart® spiral® CFL 13 watt T3 spiral 1-pack

- Use original GE's Soft White when you need a light without glare and harsh shadows.
- Saves \$37.00 in energy costs*
- Lasts 8 times longer than a 60 watt regular soft white bulb*
- \$51 in energy savings over the life of the bulb based on 3 hours per day usage
- 60 watt replacement uses only 13 watts
- Energy Star Qualified
- Estimated yearly energy costs \$1.57 based on 3 hours per day \$0.11 per kWh
- Lasts 9.1 years based on 3 hours per day usage
- Save money and save energy with GE energy smart® spiral® CFL bulbs. GE energy smart® bulbs use 75% less energy than standard incandescents, helping you save money on energy. And, because they last 8 times longer than a standard incandescent, you'll replace these bulbs less often. Use general purpose GE energy smart® spiral® CFL bulbs in common household fixtures like table lamps, floor lamps and bare lamp sockets
- T3 spiral shape with medium base for use in table lamps and enclosed fixtures
- Estimated yearly energy costs \$1.57 based on 3 hours per day \$0.11 per kWh

a product of
ecomagination



High Color Rendering
cUL Listed
Energy Savings
UL Listed



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Remove and install by grasping only plastic portion of the lamp.

Warning

- Risk of Electric Shock
 - Do not open - no user serviceable parts inside.
 - Do not use where directly exposed to water.

NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.

GENERAL CHARACTERISTICS

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	Medium Screw (E26)
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	8000.0 h
Starting Temperature (MIN)	-15.0 °C
Total Harmonic Distortion (THD) (NOM)	120.0 %
Life in Years (NOM)	9.1
Mercury Content (NOM)	3.0 mg
Picograms of Mercury (NOM)	568.2 pg
Primary Application	Standard;Facilities;Retail Display;Hospitality;Office;Restaurant

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	825.0
Mean Lumens (NOM)	660.0
Nominal Initial Lumens per Watt (NOM)	63.46154
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	13.0
Input Voltage (NOM)	120.0 V
Estimated Energy Cost per Year (NOM)	1.57
Input Current (NOM)	0.18 A
Power Factor (NOM)	0.6

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	4.900 in(124.5 mm)
Nominal Length (NOM)	4.700 in(119.4 mm)

PRODUCT INFORMATION

Product Code	74198
Description	FLE13HT3/2/SW/BX
Standard Package	Case
Standard Package GTIN	10043168741986
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168741989