



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL7524C LKG FLG NLT, 15A 125V, L1-15P

Hubbell Wiring Devices

Catalog Number	HBL7524C
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non-Grounding, Nema L1-15P, Screw Terminal, Nylon Casing, Polarized, Backwired , White.
Weight per unit	0.1500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Screw Terminals
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
insulation	Insulated Body
Material	Nylon
Number of Wires	2-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1,875
Wire Size	#18 to #10

Dimensions and Weight

Size	2.56 in x 2.56 in x 1.72 in
------	-----------------------------

Descriptions

Description	LKG FLG NLT, 15A 125V, L1-15P
extra long description	HWDC HBL7524C LKG FLG NLT, 15A 125V
Long Description	Locking Devices, Twist-Lock®, Industrial, Insulgrip® Flanged Inlet, 15A 125V, 2-Pole 2-Wire Non-Grounding, NEMA L1-15P, Screw Terminal, Nylon casing, Polarized, Backwired , White.
Product Type	LKG FLG NLT, 15A 125V, L1-15P
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585178004
Manufacturers Part Number	HBL7524C
UPC	783585178004



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Flanged Inlet

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L1-15P
standard	Certified to CSA C22.2 No. 42; Fed. Spec W-C-596; Listed to UL 498