




GE  
Lighting

**89632 - FLE15/2/A19XL**

GE A19



High Color Rendering  
cUL Listed  
Energy Savings



**GENERAL CHARACTERISTICS**

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	A19
Base	Medium Screw (E26)
Bulb Finish	Soft white
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	10000.0 h
Starting Temperature (MIN)	5.0 °C
Total Harmonic Distortion (THD) (NOM)	120.0 %
Mercury Content (NOM)	3.5 mg
Picograms of Mercury (NOM)	530.3 pg
Primary Application	Standard

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	825.0
Mean Lumens (NOM)	660.0
Nominal Initial Lumens per Watt (NOM)	55.0
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	15.0
Voltage (NOM)	120.0
Input Voltage (NOM)	120.0 V
Input Current (NOM)	0.17 A
Power Factor (NOM)	0.6

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	4.600 in(116.8 mm)
Nominal Length (NOM)	4.600 in(116.8 mm)
Bulb Diameter (DIA) (NOM)	2.375 in(60.3 mm)

**PRODUCT INFORMATION**

Product Code	89632
Description	FLE15/2/A19XL
Standard Package	Case
Standard Package GTIN	10043168896327
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168896320




GE  
Lighting

**89632 - FLE15/2/A19XL**

GE A19

 High Color Rendering  
cUL Listed  
Energy Savings



**GENERAL CHARACTERISTICS**

Lamp Type	Compact Fluorescent - Self-Ballasted
Bulb	A19
Base	Medium Screw (E26)
Bulb Finish	Soft white
Equivalent Wattage (NOM)	60.0 W
Rated Life (NOM)	10000.0 h
Starting Temperature (MIN)	5.0 °C
Total Harmonic Distortion (THD) (NOM)	120.0 %
Mercury Content (NOM)	3.5 mg
Picograms of Mercury (NOM)	530.3 pg
Primary Application	Standard

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens (NOM)	825.0
Mean Lumens (NOM)	660.0
Nominal Initial Lumens per Watt (NOM)	55.0
Color Temperature (NOM)	2700.0 K
Color Rendering Index (CRI) (NOM)	82.0

**ELECTRICAL CHARACTERISTICS**

Wattage (NOM)	15.0
Voltage (NOM)	120.0
Input Voltage (NOM)	120.0 V
Input Current (NOM)	0.17 A
Power Factor (NOM)	0.6

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	4.600 in(116.8 mm)
Nominal Length (NOM)	4.600 in(116.8 mm)
Bulb Diameter (DIA) (NOM)	2.375 in(60.3 mm)

**PRODUCT INFORMATION**

Product Code	89632
Description	FLE15/2/A19XL
Standard Package	Case
Standard Package GTIN	10043168896327
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168896320