



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HC406 2" Rigid Conn

*Abb Installation Products, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | HC406   |
| Manufacturer     | Abb Installation Products, Inc                                  |
| Description      | 2 Inch, Steel Compression Connector, For Use With Rigid Conduit |
| Weight per unit  | 0.7500 (lbs/each)   |
| Product Category | Rigid Conduit Fittings - Steel                                  |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 2" RIGID CONN   |
| extra long description | ABB HC 406 2 INCH CONN,COMP.,RGD/IM                             |
| Long Description       | 2 Inch, Steel Compression Connector, For Use with Rigid Conduit |
| Product Type           | 2 Inch Conn, Comp., RGD/Imc, Iron                               |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Steel City     |
| GTIN                      | 00785991414103 |
| Manufacturers Part Number | HC 406         |
| UPC                       | 785991414103   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type                 | Compression Couplings & Connectors   |

### Trade Size

|            |      |
|------------|------|
| Trade Size | 2 in |
|------------|------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 12   |
| Weight Per each | 0.75 |

### Uses, Certifications, and Standards

|             |                                 |
|-------------|---------------------------------|
| Application | For Use with Rigid/IMC Conduits |
| standard    | UL E23018                       |