



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HFD3030BP10 HFD 3 Pole 30 A 65 Ka At 480 Vac 600 V Max, Eaton Corp

Catalog Number	HFD3030BP10
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, HFD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 30A, 600 Vac, 250 VDC, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Load Side, 50/60 HZ, 10
Weight per unit	4.3 (lbs/each)
Product Category	3 Pole

Features

Current Rating	30 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	HFD 3 POLE 30 A 65 KA AT 480 VAC 600 V MAX,
extra long description	ETN HFD3030BP10 HFD 3P, 30 A, 65KA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, HFD, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 30A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Load side, 50/60 Hz, 10
Product Type	HFD 3P, 30 A, 65KA At 480 Vac, 600V Max

Manufacturer Information

Brand	Eaton Corp
GTIN	00786685020969
Manufacturers Part Number	HFD3030BP10
UPC	786685020969

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	4.3

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Frequency Rating standard	50/60 Hz UL Listed