



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ISPB204 2/0-14AWG 4PRT Conn

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | ISPB204   |
| Manufacturer     | Nsi Industries  |
| Description      | The Polaris ISPB2/0-4 Multi-Tap Direct Burial Single-Sided Entry Connector Features 3 Ports Sized For 2/0 - 14 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of High-Dielectric Strength Rubber Insulation. Each Single-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Radial-Tipped Set Screws. Rated For Temporary Submersion, Wet or Damp Locations and Direct Burial Applications. Installs With A Hex Key and Torque Wrench, W |
| Weight per unit  | 0.4000 (lbs/each)   |
| Product Category | Large Terminals & Connectors  |

### Features

|                      |             |
|----------------------|-------------|
| Material             | Aluminum    |
| Number of Conductors | 4           |
| Poles                | 1           |
| Voltage Rating       | 600 V       |
| Warranty             | 1 YEAR      |
| Wire Size            | 2/0-14 AWG  |
| Wire Type            | Class B & C |

### Material, Color, and Finish

|        |                       |
|--------|-----------------------|
| Color  | Black                 |
| Finish | EPDM Rubber Insulated |

### Dimensions and Weight

|      |                          |
|------|--------------------------|
| Size | L=3.65 - W=2.65 - H=2.10 |
|------|--------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 2/0-14AWG 4PRT CONN   |
| extra long description | NSI ISPB2/0-4 POLARIS EDGE Connecto   |
| Features               | The Polaris ISPB2/0-4 4-Port Single-Sided Submersible Connector provides the simplest solution for forming a secure connection between up to four conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high |
| Long Description       | The Polaris ISPB2/0-4 Multi-Tap Direct Burial Single-Sided Entry Connector features 3 ports sized for 2/0 - 14 AWG wires. The body is made from aluminum alloy wrapped in a layer of high-dielectric strength rubber insulation. Each single-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the radial-tipped set screws. Rated for temporary submersion, wet or damp locations and direct burial applications. Installs with a hex key and torque wrench, w |
| Product Type           | Polaris Edge Connector 2/0 4 Port Epdm  |
| Special Features       | (4) 2/0-14 AWG - Dual Rated   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Polaris        |
| GTIN                      | 00662381787859 |
| Manufacturers Part Number | ISPB2/0-4      |
| UPC                       | 662381787859   |

## Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | TERMINALS                       |
| Type                 | Submersible Pedestal Connectors |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 3   |
| Weight Per each | 0.4 |

## Uses, Certifications, and Standards

|                          |                             |
|--------------------------|-----------------------------|
| Application              | Wire Termination            |
| environmental conditions | 90 C                        |
| standard                 | ANSI C119.4, C119.1, UL486D |
| Temperature Rating       | 90 C                        |