



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JD3225 Type JD BRKR 3P 225A 600VAC Max 18KAIC @ 600V

Eaton Corp

Catalog Number	JD3225
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, J-Frame, JD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 225 A, 600 Vac, 250 VDC, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac, Aluminum, Line and Load, 50/60 HZ
Weight per unit	9.6 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

Features

Current Rating	225 A
dimensions	4.0600 IN X 4.1300 IN X 4.1300 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE JD BRKR 3P 225A 600VAC MAX 18KAIC @ 600V
extra long description	ETN JD3225 JD BRKR 3P 225A 600VAC M
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, J-frame, JD, Complete breaker, Fixed thermal, Fixed magnetic trip, Three-pole, 225 A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz
Product Type	JD BRKR 3P 225A 600VAC Max 18KAIC @ 600V

Manufacturer Information

Brand	Eaton
GTIN	00786679346167
Manufacturers Part Number	JD3225
UPC	786679346167

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 9.55

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

Frequency Rating 50 to 60 Hz

standard UL Listed