

BURNDY Catalog Number
UPC Number
Description
Status

K2A31U
 7818106001533
 TWO:4STR-350 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 1.94
 Length (in) 2.88
 Bolt Hole Size (in) 0.50
 Thickness 0.25
 D - in 1.69
 Pad Width (in) 1.94
 N (in) 0.88

General

Number of Holes 1
 Product Description Aluminum Universal Terminal, 2 Conductor, 1 Hole, 6 AWG (Str)-350 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range) 6 STR- 350 kcmil
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 6 AWG-350 kcmil

Physical

Installation Torque 275
 Type of Plating Tin
 Connector Type Terminal
 Bolt Hole Size 1/2
 Plated (Yes or No) N
 Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Non-Compliant
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

K2A31U
 7818106001533
 TWO:4STR-350 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in) 1.94
 Length (in) 2.88
 Bolt Hole Size (in) 0.50
 Thickness 0.25
 D - in 1.69
 Pad Width (in) 1.94
 N (in) 0.88

General

Number of Holes 1
 Product Description Aluminum Universal Terminal, 2 Conductor, 1 Hole, 6 AWG (Str)-350 kcmil, 1/2" Stud, 2 Screws, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range) 6 STR- 350 kcmil
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 6 AWG-350 kcmil

Physical

Installation Torque 275
 Type of Plating Tin
 Connector Type Terminal
 Bolt Hole Size 1/2
 Plated (Yes or No) N
 Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Non-Compliant
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175