



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL4779C LKG Conn, 15A 277V, L7-15R, BK *Hubbell Wiring Devices*

Catalog Number	HBL4779C
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 15A 277V Ac, 2-Pole 3-Wire Grounding, Nema L7-15R, Screw Terminal, Black and White Nylon.
Weight per unit	0.0820 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Pressure Screw Terminal
Current Rating	15
insulation	Insulated Body
Material	Nylon
Number of Conductors	3
pallet quantity	3600
Poles	2-Pole
Voltage Rating	277

Material, Color, and Finish

Color	Black;White
-------	-------------

Dimensions and Weight

Size	1.53 in x 1.53 in x 2.78 in
------	-----------------------------

Descriptions

Description	LKG CONN, 15A 277V, L7-15R, BK
extra long description	HWDK HBL4779C LKG CONN, 15A 277V, L
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 15A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-15R, Screw Terminal, Black and White Nylon.
Product Type	LKG Conn, 15A 277V, L7-15R, BK
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585171906
Manufacturers Part Number	HBL4779C
UPC	783585171906

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.082

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L7-15R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498