



GE  
Lighting

**65136 - GE LED PAR30**

**LED12DP30S830/35**

Energy-efficient LED lamps. Long life.

**Product Photo**



**GENERAL CHARACTERISTICS**

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26
Bulb Shape	PAR30

**PHOTOMETRIC CHARACTERISTICS**

Center Beam Candle Pwr Candela	2050 cd
Lumens per Watt (Efficacy)	63 lm
Nominal Initial Lumen per Watt	63
Rated Beam Spread	35 deg
Initial Lumens-nominal	750 lm
Color Rendering Index-CRI	84
Color Temperature	3000 K

**PRODUCT INFORMATION**

Product Code	65136
Description	LED12DP30S830/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168651363
Standard Package GTIN	00043168651363
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168651363
Alternative Unit Of Measure	CASE

**ELECTRICAL CHARACTERISTICS**

Voltage <Nom>	120 V
Rated power (Watts)	12 W



GE  
Lighting

**65136 - GE LED PAR30**

**LED12DP30S830/35**

Energy-efficient LED lamps. Long life.

**Product Photo**



**GENERAL CHARACTERISTICS**

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-PAR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26
Bulb Shape	PAR30

**PHOTOMETRIC CHARACTERISTICS**

Center Beam Candle Pwr Candela	2050 cd
Lumens per Watt (Efficacy)	63 lm
Nominal Initial Lumen per Watt	63
Rated Beam Spread	35 deg
Initial Lumens-nominal	750 lm
Color Rendering Index-CRI	84
Color Temperature	3000 K

**PRODUCT INFORMATION**

Product Code	65136
Description	LED12DP30S830/35
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168651363
Standard Package GTIN	00043168651363
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168651363
Alternative Unit Of Measure	CASE

**ELECTRICAL CHARACTERISTICS**

Voltage <Nom>	120 V
Rated power (Watts)	12 W