



GE
Lighting

39350 - null

LED7DMRX1683025

GENERAL CHARACTERISTICS

| | |
|---------------------|------------------|
| Primary Application | Track & Recessed |
| Product Technology | LED |
| Rated Life (Hours) | 25000 h |
| Base | GU5.3 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Beam Spread (range) | 25 deg |
| Center Beam Candle Pwr Candela | 1900 cd |
| Nominal Initial Lumen per Watt | 60 |
| Rated Beam Spread | 25 deg |
| Initial Lumens-nominal | 420 lm |
| Color Rendering Index-CRI | 82 |
| Color Temperature | 3000 K |

PRODUCT INFORMATION

| | |
|----------------------------------|-----------------|
| Product Code | 39350 |
| Description | LED7DMRX1683025 |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 6 |
| Ean UPC | 043168393508 |
| Standard Package GTIN | 00043168393508 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 6 |
| Sales Unit | Each |
| UCC | 043168393508 |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168393508 |
| Standard Package GTIN | 10043168393505 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168393508 |

DIMENSIONS

| | |
|-----------------------------|--------|
| Bulb Max Overall Length-MOL | 2.2 in |
|-----------------------------|--------|

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|------|
| Voltage <Nom> | 12 V |
| Input Voltage [nom] | 12 V |



GE
Lighting

39350 - null

LED7DMRX1683025

GENERAL CHARACTERISTICS

| | |
|---------------------|------------------|
| Primary Application | Track & Recessed |
| Product Technology | LED |
| Rated Life (Hours) | 25000 h |
| Base | GU5.3 |

PHOTOMETRIC CHARACTERISTICS

| | |
|--------------------------------|---------|
| Beam Spread (range) | 25 deg |
| Center Beam Candle Pwr Candela | 1900 cd |
| Nominal Initial Lumen per Watt | 60 |
| Rated Beam Spread | 25 deg |
| Initial Lumens-nominal | 420 lm |
| Color Rendering Index-CRI | 82 |
| Color Temperature | 3000 K |

PRODUCT INFORMATION

| | |
|----------------------------------|-----------------|
| Product Code | 39350 |
| Description | LED7DMRX1683025 |
| Alternative Unit Of Measure | EACH |
| Standard Package Quantity | 6 |
| Ean UPC | 043168393508 |
| Standard Package GTIN | 00043168393508 |
| No Of Items Per Sales Unit | 1 |
| No Of Items Per Standard Package | 6 |
| Sales Unit | Each |
| UCC | 043168393508 |
| Alternative Unit Of Measure | CASE |
| Standard Package Quantity | |
| Ean UPC | 043168393508 |
| Standard Package GTIN | 10043168393505 |
| No Of Items Per Sales Unit | |
| No Of Items Per Standard Package | |
| Sales Unit | Case |
| UCC | 043168393508 |

DIMENSIONS

| | |
|-----------------------------|--------|
| Bulb Max Overall Length-MOL | 2.2 in |
|-----------------------------|--------|

ELECTRICAL CHARACTERISTICS

| | |
|---------------------|------|
| Voltage <Nom> | 12 V |
| Input Voltage [nom] | 12 V |