

DESCRIPTION

The Lumark Eternalume is ideal for perimeter area lighting, residential and commercial security lighting, residential streets, parking areas, and loading platforms. U.L. listed and CSA certified unless footnoted otherwise.

SPECIFICATION FEATURES

- NEMA twistlock style photocontrol for automatic dusk-to-dawn operation
- Precision die-cut aluminum housing with natural finish
- Reactor, NPF Core and coil ballast for durable operation
- Can be pole or wall mounted. 1 5/8" O.D. slipfitter Hardware included
- Porcelain mogul- or medium-base screw shell socket with spring loaded center contact
- Fluted, formed specular aluminum reflector fastens to main housing for secure fit
- 12" open bottom, acrylic refractor
- Mercury Vapor or High Pressure Sodium Lamp Included
- U.L. listed for wet locations and CSA certified
- Approximate net weight: 11 lbs. (5 kgs.)



ETERNALUME AREA LIGHT

1 6 0 - 1 7 5 W
Mercury Vapor

7 0 - 1 5 0 W
High Pressure Sodium

LOW WATTAGE
SECURITY LUMINAIRE

ORDERING INFORMATION

Catalog Number	Lamp Type/Base	Lamp Wattage	Ballast Type/ Power Factor	Voltage	Net Wt. (lbs.)	Shipping Volume (cu. ft.)
MVEL17 2	MV/Mogul	175	Reactor/NPF	120V/60Hz	11.00	1.85
HPEL70 2	HPS/Mogul	70	Reactor/NPF	120V/60Hz	11.00	1.85
HPEL10 2	HPS/Mogul	100	Reactor/NPF	120V/60Hz	11.00	1.85
HPEL15 2	HPS/Mogul	150	Reactor/NPF	120V/60Hz	11.00	1.85

Accessories (order separately)

- OA1013=Shorting Cap
- L-A18=18" Arm with Hardware
- L-A24=24" Arm with Hardware
- EL/FSC=Full Cut-off Shield (Dark Sky Compliant)

NOTES: 1 Not U.L. Listed or CSA certified. Typically not used in U.S. or Canadian installations. 2 Includes 18" arm, lamp and 120V photocontrol. 3 For complete product data, reference the Lumark Specification binder. 4 Specifications and dimensions subject to change without notice. 5 Products also available in non-US voltages and frequencies for international markets. 6 Consult your Cooper Lighting Representative for availability and ordering information.

DESCRIPTION

The Lumark Dusklight Series is ideal for perimeter area lighting, residential and commercial security lighting, residential streets, parking areas, farm yards, and loading platforms. U.L. listed and CSA certified.

SPECIFICATION FEATURES

- NEMA twistlock style photocontrol for automatic dusk-to-dawn operation
- Precision die-cast aluminum housing with natural finish
- Reactor, NPF Core and coil ballast for long-term reliable operation. Double reinforced ballast bracket supports transformer in housing
- Porcelain mogul-base screw shell socket with spring loaded center contact
- Fluted, formed specular aluminum reflector fastens to main housing for secure fit
- 9 1/2" open bottom, acrylic refractor
- Can be pole or wall mounted. Mounting hardware supplied
- U.L. Listed and CSA certified
- Approximate net weight: 12 lbs. (5 kgs.)



DUSKLIGHT AREA LIGHT

1 7 5 W
Mercury Vapor

SECURITY LUMINAIRE

ORDERING INFORMATION

Catalog Number	Lamp Type/Base	Lamp Wattage	Ballast Type/ Power Factor	Accessories	Voltage	Net Wt. (lbs.)
LG175	MV/Mogul	175	Reactor/NPF	Arm	120V	12.00
LNH1204M	MV/Mogul	175	Reactor/NPF	No Arm	120V	7.98

NOTES: 1 For complete product data, reference the Lumark Specification binder. 2 Specifications and dimensions subject to change without notice. 3 Products also available in non-US voltages and frequencies for international markets. 4 Consult your Cooper Lighting Representative for availability and ordering information.