



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LL125DCG 1.25" Cond Body C/G

Appleton/Oz Gedney

Catalog Number	LL125DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Type:Threaded Conduit, Material: Diecast Aluminum/ Epoxy Powder Coat, UI Standard: 514A, Trade Size 1 1/4, Dimension: Length 7.87 Inches, Width 3.50 Inches, Height 2.97 Inches
Weight per unit	2.0 (lbs/each)
Product Category	Alum

### Features

Material	Die Cast Aluminum
----------	-------------------

### Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

### Dimensions and Weight

Height	2.97
Hub Size	1-1/2
Length	7.87
Width	3.5

### Descriptions

Description	1.25" COND BODY C/G
extra long description	EGS LL125DCG 1-1/4 THD ALUM LL BDY
Long Description	EMT Conduit Bodies, Type:Threaded Conduit, Material: Diecast Aluminum/ Epoxy Powder Coat, UL Standard: 514A, Trade Size 1 1/4, Dimension: Length 7.87 Inches, Width 3.50 Inches, Height 2.97 Inches
Product Type	1-1/4 THD Alum LL Bdy CVR GSKT
Special Features	1-1/4 IN Trade Size, Type LL Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #2 AWG, Volume 35.40 IN <sup>3</sup> , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

### Manufacturer Information

Brand	Appleton
GTIN	00687855000715
Manufacturers Part Number	LL125DCG
UPC	687855000715

### Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Weight Per each	2

## Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
-------------	---

standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A
----------	--