



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISR600 Polaris Conn. 600-6 *Nsi Industries*

| | |
|------------------|---|
| Catalog Number | ISR600 |
| Manufacturer | Nsi Industries |
| Description | Insulated Butt Splice, #6 Awg Conductor Size, 600 Kcmil Conductor Size, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, -45 °C (Cold) Operating Temperature, +90 °C Operating Temperature, 5.83 In Overall Length, 600 V, 1 LB |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------------|---------------|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 600 MCM-6 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Black |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=5.830 - W=1.570 - H=3.050 |
|------|-----------------------------|

Descriptions

| | |
|------------------------|------------------------------------|
| Description | POLARIS CONN. 600-6 |
| extra long description | NSI ISR-600 POLARIS Ins Splice 600 |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00662381789457 |
| UPC | 662381789457 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | IN-Line Splicer/Reducer |

Packaging

| | |
|-----------------|---|
| Carton | 2 |
| Weight Per each | 1 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 75 C |
| standard | UL 486A/B |
| Temperature Rating | 75 C |