

Heavy Duty Channel

FEATURES

- Steel housing with longitudinal ribs for extra strength
- Ballast cover retained by ¼ turn fasteners
- Individual or row mounting, surface, or suspended
- Channel ends double as joiners
- All metal parts are treated with a five stage phosphate bonding process and finished with a baked white enamel
- UL listed 1598, cUL or CSA. Damp Location standard



ORDERING INFORMATION

K							
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE		BALLAST	VOLTAGE	OPTIONS
K Heavy Duty Channel	4 4'	1 One	28 4', T5: 28 Watt		NOTE: See Technical Section for other ballast options. E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T5, T8, or T12 (96HO only), Programmed Start 4EP 4-Lamp Electronic T5HO (N/A 347V) or T8, Programmed Start	U 120V-277V 347 347V	BC1 Branch Circuit Wiring, Single Circuit (For more branch circuit wiring options see page 113) UN Full Height End Channels GLR Fast Blow Fuse EL Emergency Battery Pack PAF Paint After Fabrication NYC NYC Compliant NYCU NYC Compliant, Union Label
	8 8'	2 Two	32 4', T8: 32, 30, 28 or 25 Watt				
	16 16' (Two housings)	See Product Availability table below.	48HO 4', T12: 60 Watt 54 4', T5HO: 54 or 51 Watt 96T8 8', T8: 59 Watt 96HO 8', T12: 110 or 95 Watt 96T8HO 8', T8: 86 Watt				

For more options see pages 96-112.


ACCESSORIES (ORDER SEPARATELY)

- CSWG4** 4' Wire Guard (w/o reflector)
- CSR4** 4' Symmetric Reflector
- CSRA4** 4' Asymmetric Reflector
- S18** 18" Stem, 8° Swivel Stem and Canopy
- SS18** 18", 45° Swivel Stem and Canopy
- KHC** 24" Chain Hanger Assembly
- KTH** Tong Hanger (Pair)

For more accessories see pages 99-101.

PRODUCT AVAILABILITY

SIZE	NO. OF LAMPS IN CROSS SECTION	NO. OF LAMPS IN FIXTURE	LAMP TYPE	WIDTH	LENGTH	HEIGHT
4'	1	1	28, 32, 48HO, 54	4 3/16"	48"	2 1/2"
	2	2	28, 32, 48HO, 54	4 3/16"	48"	2 1/2"
8'	1	1	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	96"	2 1/2"
	2	2	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	96"	2 1/2"
16' (Two housings)	1	2	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	192"	2 1/2"
	2	4	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	192"	2 1/2"



Heavy Duty Channel

FEATURES

- Steel housing with longitudinal ribs for extra strength
- Ballast cover retained by ¼ turn fasteners
- Individual or row mounting, surface, or suspended
- Channel ends double as joiners
- All metal parts are treated with a five stage phosphate bonding process and finished with a baked white enamel
- UL listed 1598, cUL or CSA. Damp Location standard



ORDERING INFORMATION

MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	BALLAST	VOLTAGE	OPTIONS
K Heavy Duty Channel	4 4' 8 8' 16 16' (Two housings)	1 One 2 Two See Product Availability table below.	NOTE: See Technical Section for other ballast options. E Electronic T8, Instant Start 4E 4-Lamp Electronic T8, Instant Start EP Electronic T5, T8, or T12 (96HO only), Programmed Start 4EP 4-Lamp Electronic T5HO (N/A 347V) or T8, Programmed Start	U 120V-277V 347 347V	BC1 Branch Circuit Wiring, Single Circuit (For more branch circuit wiring options see page 113) UN Full Height End Channels GLR Fast Blow Fuse EL Emergency Battery Pack PAF Paint After Fabrication NYC NYC Compliant NYCU NYC Compliant, Union Label
LAMP TYPE					
28 4', T5: 28 Watt					
32 4', T8: 32, 30, 28 or 25 Watt					
48HO 4', T12: 60 Watt					
54 4', T5HO: 54 or 51 Watt					
96T8 8', T8: 59 Watt					
96HO 8', T12: 110 or 95 Watt					
96T8HO 8', T8: 86 Watt					

For more options see pages 96-112.

ACCESSORIES (ORDER SEPARATELY)

- CSWG4** 4' Wire Guard (w/o reflector)
- CSR4** 4' Symmetric Reflector
- CSRA4** 4' Asymmetric Reflector
- S18** 18" Stem, 8° Swivel Stem and Canopy
- SS18** 18", 45° Swivel Stem and Canopy
- KHC** 24" Chain Hanger Assembly
- KTH** Tong Hanger (Pair)

For more accessories see pages 99-101.

PRODUCT AVAILABILITY

SIZE	NO. OF LAMPS IN CROSS SECTION	NO. OF LAMPS IN FIXTURE	LAMP TYPE	WIDTH	LENGTH	HEIGHT
4'	1	1	28, 32, 48HO, 54	4¾"	48"	2½"
	2	2	28, 32, 48HO, 54	4¾"	48"	2½"
8'	1	1	28, 54, 96T8, 96HO, 96T8HO	4¾"	96"	2½"
	2	2	28, 54, 96T8, 96HO, 96T8HO	4¾"	96"	2½"
16' (Two housings)	1	2	28, 54, 96T8, 96HO, 96T8HO	4¾"	192"	2½"
	2	4	28, 54, 96T8, 96HO, 96T8HO	4¾"	192"	2½"

