



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



N250 250 Cu Split Bolt *Nsi Industries*

Catalog Number	N250
Manufacturer	Nsi Industries
Description	Split Bolt Connector, #1/0 Awg (Range Of Equal Main and Tap-Solid) Conductor Size, 250 MCM (Range Of Equal Main and Tap-Stranded); 1/0 Awg (Minimum Tap With One Maximum Main-Stranded) Conductor Size, Non-Insulated, Copper; Copperweld Conductor Material, 2 Conductors, +90 °C Operating Temperature, 2.106 In Overall Length, Split Terminal, 600 V, 0.53 LB/Ea
Weight per unit	0.5300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	1/0 STR - 250 MCM
Wire Type	Class A & B

Material, Color, and Finish

Color	Copper
Finish	COPPER

Dimensions and Weight

Size	L=2.106 - W=1.102
------	-------------------

Descriptions

Description	250 CU SPLIT BOLT
extra long description	NSI N-250 Split Bolt Copper 250
Features	Copper Split Bolt Connector 250 MCM Copper Split Bolt Connectors are high-strength solderless service connectors made of high-copper alloy for copper and copperweld wires. Type for two maximum wire sizes.

Manufacturer Information

GTIN	00662381020093
UPC	662381020093

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Copper Split Bolts



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.53

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL486B
Temperature Rating	90 C