

BURNDY Catalog Number
UPC Number
Description
Status

KA6U
 7818103701799
 14STR-6STR DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	0.50
Length (in)	1.06
Bolt Hole Size (in)	0.25
Thickness	0.09
D - in	0.63
Pad Width (in)	0.50
N (in)	0.25

General

Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 14-6 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	14 STR- 6 STR
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	14 AWG-6 AWG

Physical

Installation Torque	45
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/4
Plated (Yes or No)	Y
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us



BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

KA6U
 7818103701799
 14STR-6STR DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	0.50
Length (in)	1.06
Bolt Hole Size (in)	0.25
Thickness	0.09
D - in	0.63
Pad Width (in)	0.50
N (in)	0.25

General

Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 14-6 AWG (Str), 1/4" Stud, 1 Screw, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	14 STR- 6 STR
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	14 AWG-6 AWG

Physical

Installation Torque	45
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	1/4
Plated (Yes or No)	Y
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175