



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



P1010RL 10-14AWG #10STD Bare Ring TRML

Panduit Corporation

Catalog Number	P1010RL
Manufacturer	Panduit Corporation
Description	The P10-10R-L Pan-Term® Terminal Is A Non-Insulated, Ring Terminal. Brazed Seam Protects Terminal Barrel From Splitting During The Crimp Process. Internal Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength.
Weight per unit	0.2200 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Standard
media	Yes
Voltage Rating	2000

Descriptions

Description	10-14AWG #10STD BARE RING TRML
extra long description	PAN P10-10R-L Pan-Term® P10-10R-L R
Long Description	The P10-10R-L Pan-Term® Terminal is a non-insulated, ring terminal. Brazed seam protects terminal barrel from splitting during the crimp process. Internal barrel serrations assure good wire contact and maximum tensile strength.
Product Type	Pan-Term® P10-10R-L Ring Terminal, Bare, 10-14 Awg, #10 Stud

Manufacturer Information

Brand	PANDUIT
GTIN	00074983802326
Manufacturers Part Number	P10-10R-L
UPC	074983802326

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Packaging

Carton	50
Package	500
Weight Per each	0.22

Uses, Certifications, and Standards

Enclosure	Ring shape
Temperature Rating	302 Degrees Fahrenheit (150 Degrees Celsius)