ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PH50PG 50 Va Mte CTRL XFRMR 120X240V-12X24V

Hammond Power Solutions

Catalog Number	PH50PG
Manufacturer	Hammond Power Solutions
Description	Machine Tool Rated Molded Industrial Control Transformer, 120X240 PV, 12X24 SV, 50va
Weight per unit	3.5 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

Wattage	50

Dimensions and Weight

Height	3.19
Length	4.38
Width	3

Descriptions

Description	50 VA MTE CTRL XFRMR 120X240V-12X24V
extra long description	HMND PH50PG CNTL 50VA 120x240-12x24
Long Description	Machine Tool Rated Molded Industrial Control Transformer, 120x240 PV, 12x24 SV, 50VA
Product Type	CNTL 50VA 120X240-12X24
Special Features	Potted control transformer for high inrush applications powering coils. Options include finger safe cover and an innovative fuse holder system.

Manufacturer Information

Brand	HPS Imperator™
GTIN	00803423078126
Manufacturers Part Number	PH50PG
UPC	803423078126

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Molded

Packaging

Carton	1
Weight Per each	3.5

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Automation, Panel shops, Machines, Solenoids, Control Applications, Timers
Enclosure	Core and Coil
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum